

LOBSTER HOLDING DEVICES

PRESET



		HOLDING DEVICE SMALL						
		Lobster size 1		Lobster size 2		Lobster size 3		
MM	hole no.	50 - 90	80 - 150	150 - 250	50 - 90	80 - 150	150 - 250	
Inches		1,97-3,54	3,15-5,91	5,91-9,84	1,97-3,54	3,15-5,91	5,91-9,84	
ANSI B16.5	R 12	2	R 21	4	R 36	2		
	R 13	3	R 22	3	R 37	2(300-600) 4(900)		
	R 14	3	R 23	3(300-600) 4(2500)	R 38	5		
	R 15	2	R 24	4	R 39	5		
	R 16	3	R 25	3	R 40	2		
	R 17	2	R 26	3(300-600) 5(2500)	R 41	3(300-600) 4(900)		
	R 18	3	R 27	5	R 42	5		
	R 19	2	R 28	6	R 43	2		
	R 20	3(600) 4(1500)	R 29	3	R 44	5		
			R 30	3	R 45	3(300-600) 4(900)		
			R 31	3(300-600) 4(900)	R 46	5		
			R 32	6	R 47	6		
			R 33	3	R 90	5		
			R 34	3	R 92	6		
			R 35	5	R 99	7		
	API 6A	RX 20	5	RX 23	3	RX 37	3(2000) 4(3000)	
		RX 205	3	RX 24	4	RX 39	4	
				RX 25	5	RX 41	4(2000) 4(3000)	
				RX 26	3	RX 44	5	
				RX 27	5	RX 45	4(2000) 4(3000)	
			RX 31	3(2000) 4(3000)	RX 46	5		
			RX 35	5	RX 47	6		
					RX 90	5		
					RX99	7		
	BX 150	4	BX 153	5(10000-15000) 7(20000)	BX 156	6(10000) 7(15000) 10(20000)		
	BX 151	4(10000) 5(15000) 6(20000)	BX 154	5(10000) 5(15000) 8(20000)	BX 169	5		
	BX 152	5	BX 155	6(10000) 7(15000) 10(20000)	BX 170	7		
	IX 40	3	IX 65	3	IX 125	2		
	IX 50	3	IX 80	4	IX 150	4		
	IX 65	5	IX 100	4	IX 200	6		



		HOLDING DEVICE LARGE							
		Lobster size 4		Lobster size 5		Lobster size 6		Lobster size 7	
MM	hole no.	250 - 350	350 - 500	500 - 800	800 - 1085	250 - 350	350 - 500	500 - 800	800 - 1085
Inches		9,84-13,78	13,78-19,69	19,69-31,50	31,50 - 42,72	9,84-13,78	13,78-19,69	19,69-31,50	31,50 - 42,72
ANSI B16.5	R 48	2	R 55	6	R 68	1	R 94	1(300) 2(600)	
	R 49	2(300-600) 4(900)	R 56	1	R 69	1(300) 2(600)	R 95	1(300) 2(600)	
	R 50	5	R 57	2(300-600) 4(900)	R 70	3	R 96	1(300) 2(600)	
	R 51	5	R 58	5	R 71	5	R 97	1(300) 2(600)	
	R 52	2	R 59	2	R 72	1	R 98	1(300) 2(600)	
	R 53	3(300-600) 5(900)	R 60	6	R 73	2(300-600)	R 101	4(900)	
	R 54	5	R 61	3(300-600)	R 74	3	R 102	4(900)	
	R 91	2	R 62	4	R 75	5	R 103	4(900)	
			R 63	6	R 76	1	R 104	5(900)	
			R 64	2	R 77	2(300-600)	R 105	5(900)	
			R 65	3(300) 4(600)	R 78	4			
			R 66	4	R 79	8			
			R 67	7	R 80	7			
					R 81	7			
					R 93	9			
				R 100	4(900)				
API 6A	RX 49	3(2000) 4(3000)	RX 57	3(2000) 4(3000)	RX 69	2(2000)			
	RX 50	5	RX 63	6	RX 70	3			
	RX 53	4(2000) 5(3000)	RX 65	7	RX 73	2			
	RX 54	5	RX 66	6	RX 74	3			
	RX 91	5							
	BX 157	5(5000) 7(10000) 10(20000)	BX 158	5(10000) 8(15000) 9(20000)	BX 163	4	BX 303	3	
	BX 171	4	BX 159	7(10000) 9(15000)	BX 164	7(10000) 9(15000)			
	BX 172	6	BX 160	5	BX 165	5			
			BX 161	6	BX 166	8			
			BX 162	6(5000) 8(10000)	BX 167	3			
					BX 168	5			
	IX 250	4	IX 350	4	IX 500	2	IX 750	2	
	IX 300	6	IX 400	6	IX 550	2	IX 800	3	
			IX 450	7	IX 600	4	IX 850	3	
					IX 650	5	IX 900	4	
					IX 700	6	IX 950	5	
				IX 750	6	IX 1000	5		